

Customer: [REDACTED]

Machine Used: TensileTurn – Industrial Upgrade Model

Date: [REDACTED]

Prepared By: [REDACTED]

Machined Specimens:

- Standard ASTM 0.350" round bar specimen
- Standard ASTM 0.505" round bar specimen
- Non-Standard ASTM 0.505" round bar specimen

Machining Conditions:

All specimens were machined using Hysol MB10 coolant, with cutting parameters tailored to suit the material properties. A tailstock was used to provide additional support during machining.

Specimens were pre-center-drilled prior to the turning operations. Due to their square cross-section, all parts were secured using a 4-jaw independent chuck for proper alignment and stability.

Turning Operations:

Operation 1: Roughing and finishing of the outer diameter

- **Tool:** SDJCR, Radius: 0.0157"

Operation 2: Finishing of the outer diameter (right side)


- **Tool:** SDJCL, Radius: 0.0157"

Operation 3: Cut-off operation


Notes:

- Aside from the non-round cross-sectional shape, no major difficulties were encountered during machining.
- The Non-Standard ASTM 0.505" specimen had a long and narrow geometry, making it prone to vibration and chatter, particularly during the finishing stage. To mitigate this, the surface speed was significantly reduced, resulting in a duller (opaque) finish, though dimensional accuracy remained within acceptable limits.
- All specimens were machined under standard testing conditions. Customers performing continuous machining may benefit from optimizing feeds, speeds, and tool selection to improve efficiency and surface quality.
- Machining was performed in alignment with the requirements outlined in ASTM E8.






ASTM E8 Schematic Representation




ASTM E8 Test Sample – Dimensional Reference



Cutting Conditions – By Specimen:**Standard ASTM 0.350" Round Bar Specimen:**

- **Surface Speed (SFM):** 600 feet/minute
- **Feed per Revolution:** 0.004 inches/rev
- **Depth of Cut:** 0.0035 inches per radial pass
- **Cycle Time:** 7 minutes
- **Video Link:** 

**Standard ASTM 0.505" Round Bar Specimen:**

- **Surface Speed (SFM):** 600 feet/minute
- **Feed per Revolution:** 0.004 inches/rev
- **Depth of Cut:** 0.0035 inches per radial pass
- **Cycle Time:** 7 minutes
- **Video Link:** 



Non-Standard ASTM 0.505" Round Bar Specimen:

- **Surface Speed (SFM):** 600 feet/minute (initial); reduced to 100 feet/minute for finishing
- **Feed per Revolution:** 0.004 inches/rev
- **Depth of Cut:** 0.0035 inches per radial pass
- **Cycle Time:** 20 minutes
- **Video Link:** 